

DOUBLE EYE CLOSED MESH CABLE SUPPORT SOCKS

⚠ WARNING

Cancer and Reproductive Harm: www.P65Warnings.ca.gov



KEY FEATURES

- ✓ Made from 304 stainless steel
- ✓ Designed for two connect/support points

Double eye closed mesh support sock in 304 stainless steel. Two eyes for two connect/support points. Closed mesh for when end of cable is available.

Slingco Part No.	Approx. Break Load (lb)	Approx. Break Load (kg)	Lattice Length (in)	Lattice Length (mm)	Lattice Material	Range (in)	Range (mm)
ZCS2038	512	230	9.7	247	304 Stainless	0.50 - 0.63	12 - 16
ZCS2039	740	335	9.7	247	304 Stainless	0.63 - 0.75	16 - 19
ZCS2040	1,000	450	13	331	304 Stainless	0.75 - 1.00	19 - 25
ZCS2041	1,540	695	15	344	304 Stainless	1.00 - 1.25	25 - 31
ZCS2042	1,540	695	16.5	382	304 Stainless	1.25 - 1.50	31 - 38
ZCS2043	2,010	910	15	420	304 Stainless	1.50 - 1.75	38 - 44
ZCS2044	2,300	1,465	21	509	304 Stainless	1.75 - 2.00	44 - 50
ZCS2045	3,230	1,465	24	535	304 Stainless	2.00 - 2.50	50 - 63
ZCS2046	4,000	1,815	26	611	304 Stainless	2.50 - 3.00	63 - 76
ZCS2047	4,000	1,815	29	662	304 Stainless	3.00 - 3.50	76 - 89
ZCS2048	4,000	1,815	29	738	304 Stainless	3.50 - 4.00	89 - 102
ZCS6404	4,000	1,815	30	762	304 Stainless	4.00 - 4.50	102-114
ZCS6405	4,000	1,815	30	762	304 Stainless	4.50 - 5.00	114-127
ZCS6406	4,000	1,815	30	762	304 Stainless	5.00 - 5.50	127-140



L9, 1 York Street, Sydney, NSW 2000, Australia Sales: +61 3 8840 6556

GET IN TOUCH

+61 3 8840 6556

sales@slingcoaustralia.com.au

DOUBLE EYE CLOSED MESH CABLE SUPPORT SOCKS

This information is for marketing purposes only. The details contained herein is presented as general information and no representation or warranty is expressly or impliedly given as to its accuracy, completeness or correctness. It does not constitute part of a legal offer or contract. For technical specifications, please contact Slingco Australia Pty. Ltd

Dimensions

The figures shown are indicative only. Fully dimensioned data-sheets are available on request. Nominal figures/actuals are as per data-sheet with tolerances of +/-10%. Please contact us if you have any questions.

Range dimension overlaps If the cable, rope or hose you have lies where ranges overlap, e.g. 1" when sizing is 0.5-1.00 and 1.00-1.5 we recommend that you select your cable grip to achieve break load first. If tensile strengths are equal or both adequate, choose the smaller of the two. Please contact us if you have any questions.



L9, 1 York Street, Sydney, NSW 2000, Australia Sales: +61 3 8840 6556

GET IN TOUCH



+61 3 8840 6556



sales@slingcoaustralia.com.au